


**ENGINEERED
ELECTRONICS, INC.**

**VISUAL PATIENT
STATION
900-535**

FEATURES

- * LED INDICATORS PER BED**
- * AUTOMATIC CALL WHEN CALL CORD IS REMOVED**
- * SINGLE OR DUAL DOME AND POINT OUTPUTS**
- * PLUG-IN CONNECTIONS**
- * SINGLE GANG MOUNT WITH NO SUBASSEMBLIES**



GENERAL DESCRIPTION

The EEI model 900-535 Visual Patient Station provides a means for patient to signal a nurse when assistance is required. The nurse must go to patient room to clear the call from system.

ENGINEERS' SPECIFICATIONS

- | | |
|--|--|
| (1) The equipment described shall be manufactured and assembled entirely in the United States of America. | (6) Removal of a call cord either intentionally or accidentally shall place a normal call that cannot be reset until the cord is secured in the station. |
| (2) The station shall be solid state transistor circuitry mounted on a single gang face plate, requiring two 6/32 screws for mounting. | (7) A connector shall be provided with color coded wires for prewiring, quick install and removal of device. |
| (3) The station shall have two red call assurance LEDs which will operate independent of each other. | (8) There shall be a jumper on PCB for selecting either one or two point and dome outputs. |
| (4) There shall be a single reset switch for clearing routine calls on the station. | (9) The location of the station shall be as indicated one either prints _____ inches above the finished floor. |
| (5) Two 1/4" phone jacks shall be provided to accommodate any type of normally open call cord device. | (10) The station shall conform to Underwriters' Laboratory, Inc. standard (U.L. 1069). |

REV 1/04/21



ENGINEERED ELECTRONICS, INC. * 4301 INDUSTRIAL ACCESS ROAD * DOUGLASVILLE, GA. 30134

ASSOCIATED EQUIPMENT


Included

- 2 - 100-023 Dummy Plugs
- 2 - 100-195 1-1/4 inch 6/32 countersunk
phillips head machine screws.
- 1 - 500-193 Pigtail Connector

Not Included

- 900-800 Oxygen Call Cord 10 ft.
- 900-800-C Oxygen Call Cord 10 ft
- 900-801 Call Cord 6 ft.
- 900-802 Call Cord 10 ft.
- 900-804 Geriatric Presscall Cord 10 ft
- 900-804-C Geriatric Presscall Cord 10 ft
- 900-804-Pad-C Geriatric Pad Call Cord 10 ft
- 900-806 Breath Call Cord 9 ft.
- 900-807 Call Cord 7 ft
- 900-817 Dual Call Cord 10 ft
- 900-819 Call Cord 10 ft W/ Locking Push Button
- 500-188 Pigtail Connector(For Dual outputs)

WIRING DIAGRAM



IMPORTANT NOTE:

Be sure to remove or cap unused wires.

OPTIONS

One or two point wire outputs

ELECTRICAL

Volts - 24 VDC
AMPS (standby) - 6 MA
AMPS (max) - 52 MA

USEABLE BACK BOXES FOR NEW CONSTRUCTION

Steel City - CDLE, 58371,6060-02 or any single gang outlet box 2 1/2 inches deep with a minimum of 12.5 cubic inch capacity.