

Kensington Overbed Light

Timeless, residential style elevates decor.

Features:

The Kensington Overbed Light is a great solution for overbed applications. The fixture contains two ballasts and is available with or without a 4-position pull switch for direct and indirect lighting requirements. A nightlight is included with the fixture. The Crown Molding frame is made of real wood and available in a variety of colors. There is a frosted white bottom diffuser and clear acrylic top panel for indirect lighting.

Construction:

The housing is die-formed from 22-gauge steel and includes standard mounting holes and wiring access.

Finish:

The frame is constructed from real wood and is available unfinished or in the following painted finishes: Off-White, Oil-Rubbed Bronze and Latte.



Electrical (LED):

Input: 120VAC / 60 Hz, 0.7A Max Not compatible with dimmers.

Electrical (Fluorescent):

This unit is wired with two UL listed electronic high-power factor instant-start ballasts for one up, two down T8 lamps at 120V-50/60 Hz AC operation. 4-position, 3-circuit pull switch (on up, on down, on both, all off) is standard and located toward the right end. LED nightlight and on/off pull switch are included.

LED

Off-White*	LED	Source Lumen	ССТ	Features
#2C878	60W	1250 up/2700 down		4-Way Pull Swite
#2C786	0077	1350 up/2700 down	2000K	Wall Switch
#2C817	80W	1900 up/2600 dour	- 3000K	4-Way Pull Swite
#2C872	8000	1800 up/3600 down		Wall Switch

Fluorescent

riuorescent								
Off-White*	Lamping	Source Lumen	ССТ	Features	Dimensions			
#2C823		1350 up/2700 down		4-Way Pull Switch	41‰"L x 7½"D x 5½"H			
#2C861	32W/3-Bulb	1350 up/2700 down			41710 L X 775 D X 375 H			
#2C792	32VV/3-DUID	1000	3000K	4-Way Pull Switch	53‰"L x 7⅔"D x 5⅔"H			
#2C808		1800 up/3600 down		Wall Switch	55710 L X 775 D X 575 H			

Maxwell Thom

Certification:

cETLus listed for damp locations and ADA compliant.

Diffuser:

The top diffuser is made from .10" clear acrylic sheet and the bottom diffuser is frosted white .10" thick sheet.

LED:

Integrated LED modules are capable of producing a total of 4050 source lumen for 38" or 5400 source lumen for 50" in 3000K CCT. Rated for 50,000 hours and 90 CRI.

Options:

4-Way Pull Switch or Wall Switch (refer to ordering information).


Lamping:

For use with 3/25 or 3/32 Watt T8 linear fluorescent lamps.

Warranty:

Limited warranty: This fixture is free from defects in materials and workmanship for a period of five years from date of purchase.


Specifications and dimensions subject to change without notice.



Features	Dimensions
4-Way Pull Switch	41‰"L x 7½"D x 5½"H
Wall Switch	41/10 E X 7 / 5 B X 6 / 5 H
4-Way Pull Switch	53‰"L x 7%"D x 5%"H
Wall Switch	JJ / 10 L X / /5 D X J /5 II

1-800-634-7328 / maxwellthomas.com

Kensington Overbed Light



Foot-candles are measured at 66", 69", 72" and 75" heights and 0", 12", 24", 36" and 48" away from the wall. Three measurements at each height and distance are taken for the uplight, downlight and up/downlight combination.

36" Kensington LED Overbed Light (UPLIGHT ONLY)

	1010	easuring	Distance		dli
	0"	12"	24"	36"	48"
p. 75	" 1.5	2.4	2.9	2.9	2.7
훈통 72	" 1.4	2.4	2.8	2.8	2.7
∃∄ 69	" 1.3	2.4	2.8	2.7	2.5
≥ 66	13	23	27	27	2.6

36" Kensington LED Overbed Light (DOWNLIGHT ONLY) Measuring Distance from Wall

		0"	12"	24"	36"	48"	
Ð	75"	46.6	43.9	29.0	15.7	8.2	
불불	72"	54.9	48.8	30.9	14.7	7.6	
hei	75" 72" 69"	63.9	57.8	33.2	15.1	7.3	
Σ_	66"	77.3	68.5	36.4	14.4	6.6	

36" Kensington LED Overbed Light

(UPLIGHT 8	& DOWNI	_IGHT)			
	Me	asuring	Distance	from W	all
	0"	12"	24"	36"	48"
<u>∞</u> 75"	48.7	46.0	31.4	18.5	11.0
eight "25" "	55.2	57.1	33.2	18.2	10.3
0 <u>7</u> 09	66.5	60.7	34.7	17.3	9.9
≊ 66"	79.0	70.4	35.6	16.7	9.2

48" Kensington LED Overbed Light (UPLIGHT ONLY)

		IVIE	asuring	Distance		all	
		0"	12"	24"	36"	48"	
<u>5</u>	75"	1.8	2.9	3.6	3.6	3.5	
nting ght	72"	1.7	2.9	3.5	3.6	3.4	
Moun Hei	69"	1.7	3.0	3.5	3.5	3.3	
Σ	66"	1.5	2.9	3.4	3.4	3.2	

48" Kensington LED Overbed Light (DOWNLIGHT ONLY) Measuring Distance from Wall

		0"	12"	24"	36"	48"
p. 7	'5"	57.8	55.6	35.4	19.8	10.5
훈통 7	'2"	67.3	61.4	37.1	18.7	9.8
Mounting Height 9 2 /	9"	77.6	71.4	38.5	18.4	9.2
≥ 6	6"	93.9	80.9	39.5	17.9	7.6

48" Kensington LED Overbed Light (UPLIGHT & DOWNLIGHT)

0	Me		Distance	from	Wall
	0"	10"	24"	201	

	0	12	Z4 "	30	48
<u>∞</u> 75"	59.5	57.4	38.7	22.5	14.1
founting Height 69 "69"	69.0	65.3	41.4	22.9	13.3
∃∰ 69"	79.3	73.8	44.7	22.5	12.8
≥_ 66"	95.5	82.4	42.1	19.9	11.2

Maxwell Thomas

36" Kensington FLR 2-Bulb Overbed Light (UPLIGHT ONLY) Measuring Distance from Wall Measuring Distance from Wall

			acang			
		0"	12"	24"	36"	48"
D.	75"	2.4	3.6	3.9	3.8	3.6
Height	72"	2.4	3.6	3.9	3.8	3.6
Ŧ	69"	2.6	3.9	4.0	3.9	3.6
	66"	2.7	3.9	4.0	3.8	3.7

Mounting

lou

	0"	12"	24"	36"	48"
5"	28.7	27.1	18.4	10.5	5.8
2"	34.5	32.5	19.7	11.2	6.0
)"	38.4	40.1	22.4	10.9	5.4
5"	50.8	45.9	24.8	10.3	5.3
	5" 2" 9"	5" 28.7 2" 34.5 38 .4	5 " 28.7 27.1 3 4.5 32.5 3 8.4 40.1	28.7 27.1 18.4 34.5 32.5 19.7 38.4 40.1 22.4	28.7 27.1 18.4 10.5 2" 34.5 32.5 19.7 11.2 38.4 40.1 22.4 10.9

36" Kensington FLR 2-Bulb Overbed Light (UPLIGHT & DOWNLIGHT)

		Measuring Distance from Wall							
		0"	12"	24"	36"	48"			
n	75"	30.9	30.8	22.0	14.2	9.8			
Height	72"	38.3	37.8	24.9	14.4	9.6			
	69"	40.9	42.2	25.9	14.2	9.6			
_	66"	53.5	49.7	27.7	15.0	8.8			

Measuring Distance from Wall

		0"	12"	24"	36"	48"			
<u>5</u>	75"	2.7	4.0	4.7	4.8	4.8			
Mounting Height	72"	2.6	4.0	4.6	4.6	4.4			
년 G	69"	2.4	3.8	4.5	4.4	4.5			
Σ_	66"	2.4	4.2	4.6	4.3	4.3			

48" Kensington FLR 2-Bulb Overbed Light (DOWNLIGHT ONLY) Measuring Distance from Wall Measuring Distance from Wall Measuring Distance from Wall

		0"	12"	24"	36"	48"	
Mounting Height	75"	41.2	39.0	25.0	13.5	7.8	
	72"	48.5	44.6	26.7	13.6	7.7	
	69"	56.6	51.8	29.4	13.7	6.9	
	66"	63.8	59.5	29.5	12.7	6.1	

48" Kensington FLR 2-Bulb Overbed Light (UPLIGHT & DOWNLIGHT)

		Measuring Distance from Wall							
		0" 12" 24" 36" 4							
Ð	75"	44.5	43.2	29.1	18.2	12.7			
jt ji	72"	51.8	49.9	32.2	18.8	12.5			
Те;	69"	60.0	56.4	34.0	18.2	11.4			
≥ _	66"	67.4	64.3	34.7	17.67	10.5			

		weasuring Distance from wall						
		0"	12"	24"	36"	48"		
5	75"	2.6	3.7	3.8	3.7	3.6		
불봄	72"	2.5	3.7	4.1	4.0	3.8		
Теі	69"	2.6	3.7	4.0	3.9	3.6		
Σ_	66"	2.7	4.0	4.1	3.8	3.6		

36" Kensington FLR 2-Bulb Overbed Light (DOWNLIGHT ONLY) Measuring Distance from Wall 36" Kensington FLR 3-Bulb Overbed Light (DOWNLIGHT ONLY) Measuring Distance from Wall

mouounig Diotanoo nom man						

36" Kensington FLR 3-Bulb Overbed Light (UPLIGHT & DOWNLIGHT)

		Measuring Distance from Wall						
		0"	12"	24"	36"	48"		
p _	75"	35.9	35.2	25.3	15.0	10.5		
불불	72"	44.0	43.3	28.8	16.7	10.1		
Hei	69"	49.2	47.0	27.1	14.8	9.3		
Σ	66"	61.5	55.6	31.4	16.1	9.4		

48" Kensington FLR 2-Bulb Overbed Light (UPLIGHT ONLY) 48" Kensington FLR 3-Bulb Overbed Light (UPLIGHT ONLY)

		Measuring Distance from Wall						
		0"	12"	24"	36"	48"		
p. 7	5"	2.7	4.0	4.7	4.8	4.8		
ght 2	2" `	2.6	4.0	4.6	4.6	4.4		
6 Her	9" `	2.4	3.8	4.5	4.4	4.5		
≥ 6	6" [`]	2.4	4.2	4.6	4.3	4.3		

	0"	12"	24"	36"	48"	
<u>∞</u> 75"	42.5	39.7	26.1	14.0	7.6	
훈통 72"	48.2	46.0	28.3	13.9	7.4	
Mounting Height 69" 69" 69" 60"	55.9	51.2	27.4	13.5	6.9	
≊ [_] 66"	69.4	63.5	30.4	14.1	6.4	

48" Kensington FLR 3-Bulb Overbed Light (UPLIGHT & DOWNLIGHT)

Measuring Distance from Wall O" 12" 24" 36" 48" 45.3 44.7 30.8 19.5 12.9 53.3 51.5 32.8 19.0 16.9 58.4 56.3 34.0 17.9 11.1 73.1 67.1 34.7 18.3 10.9 75" 72" _ 69" _

1-800-634-7328 / maxwellthomas.com

